

## Pneumatic needle gun MDNE 19

**MANNESMANN  
DEMAG**

### Application:


For cleaning work, especially to remove rust and paint.

### Version:

- With lever start function
- With pistol grip
- Exhaust air: front
- Frequency 110 Hz
- Vibration level  $\leq 5 \text{ m/s}^2$

### Delivery:

Needle set (kit contents: 19 needles  $\text{\O}3.2 \text{ mm} \times 140 \text{ mm}$ )



<b>Art. no.</b>	<b>75061 460</b>
<b>Model</b>	MDNE 19
<b>Max. impact rate</b>	6600 rpm
<b>Air consumption</b>	1.9 l/s
<b>Number of needles</b>	19
<b>Diameter of needle</b>	3.2 mm
<b>Connection thread</b>	IT 1/4 inch
<b>Inner hose diameter</b>	10 mm
<b>Sound-pressure level</b>	89 dB
<b>Vibration</b>	3.2 m/s <sup>2</sup>
<b>Length</b>	272 mm
<b>Weight</b>	2.4 kg

### EAN-Code

4251757301988