


PXF4051AAJ Datasheet

Product Name // 450 M, Single Mode, Cabled, Inline fiber connector

[View Product Page](#)



// Product Description:

- ⬢ Inline Fiber Connector to LC type Connector
- ⬢ Sealed to IP66, IP68, IP69K when mated with compatible connector
- ⬢ no cable options, or pre-terminated from 5M - 450M available
- ⬢ Simplex LC type fiber connector
- ⬢ Choices of OS1, OM1 and OM3 cables for single or multimode
- ⬢ PXP4082 Sealing Cap available separately to maintain IP rating of unmated connectors
- ⬢ Mate with flex fiber connector PXF4050

// General Information:

Product Configurator:	No
Product Display Title:	Inline Fiber Connector to LC type Connector
Product Family:	Circular Fiber Connectors
Product Series:	4000 Series - Simplex LC Fiber Buccaneer
Pdfbuilder Enabled:	Yes
Diameter Over Coupling Ring Mm:	19.7mm
Fibre Mode:	OS1
Function:	Inline to LC Connector Double Ended Fiber Cable
Ip Rating:	IP66, IP68, IP69K
Max Operating Temperature:	+70°C
Min Operating Temperature:	-20°C
Product Technical Image:	/p/x/pxf4051xxx_diagram.jpg

// Electrical Specifications:

Contact Type:	LC Fiber
---------------	----------

// Mechanical Specifications:

Coupling Type:	30 Degree coupling
----------------	--------------------

// Material Information:

Body Material:	Polycarbonate/Polybutylene Terephthalate (PC/PBT)
Flamability Rating:	UL94V-0

// Product PDF Links

[4000 Series Fiber connectors...](#)

// Product 3D CAD Model Links

[PXF4051AAJ3D CAD Model](#)