





FIELDLED EVO 280_96 Einbau, 280 mm, 24V DC

Artikel-Nr.: 153010-11
EAN: 4260556625430

Bestell-Nr.: 153010-11
Modell: FIELDLED EVO 96 Einbau
Bauform: LED Einbauleuchte für Maschinen
Leuchtmittel: SMD LED
Lampenleistung: ~19 W
Lampenlichtstrom: 3000 lm
Lampenlichtausbeute: 155 lm/W
Lichtverteilung: direkt
Lichtfarbe: Tageslichtweiß (5200 - 5700K)
Anschlusswert Leuchte: 24V DC \pm 10%
Anschluss Leuchte: M12 Sensorstecker A-kodiert, stirnseitig
Schutzart: IP67/IP69K
Schutzklasse: III
Entblendung: Mikroprismen
Abstrahlwinkel: 100°
Betriebstemperatur: -30... +60 °C
Farbwiedergabe (Ra): > 85
Lampenlebensdauer: > 60.000 h
Material Gehäuse: Aluminium
Material Abdeckung: ESG (Sicherheitsglas), splitterfrei
Höhe [B] x Breite [C]: 30 x 96 mm, Rahmen: 5,6 x 132 mm
Länge [A]: 280 mm, Rahmen: 336 mm
Gewicht: ~1100 g
Bruttogewicht: ~1450 g
Risikogruppe: freie Gruppe
Dimmbar: optional über Zubehör
Kennzeichnung: CE, ETL Listed
Gefertigt in: Deutschland





Lampenlebensdauer in Betriebsstunden (L80/B10)



FIELDLED EVO 280_96 Einbau, 280 mm, 24V DC

Item number: 153010-11
EAN: 4260556625430

Order number: 153010-11
Model: FIELDLED EVO 96 Einbau
Type: LED recessed luminaire for machines
Illuminant: SMD LED
Power consumption: ~19 W
Lamp luminous flux: 3000 lm
Lamp luminous efficiency: 155 lm/W
Light distribution: direct
Light colour: daylight white (5200 - 5700K)
Connected load: 24V DC \pm 10%
Connection: M12 sensor connector, A-type encoded, front-end
Degree of protection: IP67/IP69K
Class of protection: III
Glare-free: microprism
Beam angle (optics): 100°
Operating temperature: -30... +60 °C
Colour rendering (Ra): > 85
Lamps lifetime: > 60,000 h
Housing material: aluminium
Cover material: ESG (toughened safety glass), shatterproof
Height [B] x Width [C]: 30 x 96 mm, frame: 5,6 x 132 mm
Length [A]: 280 mm, frame: 336 mm
Weight (net): ~1100 g
Gross weight: ~1450 g
Risk group (DIN EN 62471): free group
Dimmable: via optional accessory
Marking: CE, ETL Listed
Made in: Germany



Lamps lifetime in operation hours (L80/B10)