



HDS-Series – Solder Cup

Material Specification:


Insulator:	Glass filled Polyester, Black UL94 V-0
Shell:	Stamped Steel, Tin Plated
Contacts:	Copper Alloy Class 3: 100 inserts min.
Contact Plating:	Selective Gold over Nickel



Size	A	B	C	E	F	G
HD15	16,33	24,99	30,81	1,145	2,99	16,62
HD26	24,66	33,32	39,14	1,145	2,99	25,25
HD44	38,38	47,04	53,04	1,145	2,99	38,96
HD62	54,84	63,50	69,32	1,205	2,41	55,25

Size 78 available on request.

Order Codes - Standard Type - with Ø 3.05mm Through Hole




Plug Connector		
15	2101-0300-01	HDS-15-MTBS
26	2101-0300-02	HDS-26-MTBS
44	2101-0300-03	HDS-44-MTBS
62	2101-0300-04	HDS-62-MTBS
78	On request	

Socket Connector		
09	2101-0300-11	HDS-15-FTBS
15	2101-0300-12	HDS-26-FTBS
25	2101-0300-13	HDS-44-FTBS
37	2101-0300-14	HDS-62-FTBS
78	On request	



D-Sub Connectors


Order Codes - Option K - Back Nut UNC 4-40



Plug Connector		
15	2101-0301-01	HDS-15-MTBS-K
26	2101-0301-02	HDS-26-MTBS-K
44	2101-0301-03	HDS-44-MTBS-K
62	2101-0301-04	HDS-62-MTBS-K
78	On request	

Socket Connector		
09	2101-0301-11	HDS-15-FTBS-K
15	2101-0301-12	HDS-26-FTBS-K
25	2101-0301-13	HDS-44-FTBS-K
37	2101-0301-14	HDS-62-FTBS-K
78	On request	


Order Codes - Option J - Front Nut UNC 4-40



Plug Connector		
15	2101-0302-01	HDS-15-MTBS-J
26	2101-0302-02	HDS-26-MTBS-J
44	2101-0302-03	HDS-44-MTBS-J
62	2101-0302-04	HDS-62-MTBS-J
78	On request	

Socket Connector		
09	2101-0302-11	HDS-15-FTBS-J
15	2101-0302-12	HDS-26-FTBS-J
25	2101-0302-13	HDS-44-FTBS-J
37	2101-0302-14	HDS-62-FTBS-J
78	On request	

Order Codes - Option KJ - Back Nut + Screw Nut UNC 4-40



Plug Connector		
15	2101-0303-01	HDS-15-MTBS-KJ
26	2101-0303-02	HDS-26-MTBS-KJ
44	2101-0303-03	HDS-44-MTBS-KJ
62	2101-0303-04	HDS-62-MTBS-KJ
78	On request	

Socket Connector		
09	2101-0303-11	HDS-15-FTBS-KJ
15	2101-0303-12	HDS-26-FTBS-KJ
25	2101-0303-13	HDS-44-FTBS-KJ
37	2101-0303-14	HDS-62-FTBS-KJ
78	On request	

