



13	742300	Hexagon socket head cap screw ISO 4762-M4x14	4	3	-	2,2
12	9400029901	Han HPR HPTC coding-element	2			
11	9110026236	Han HPR HPTC 850/1400-fe.-cont.-185mm ²	1			
10	19400020810_03	Han HPR HPTC 850/1400 CS-HB-c.-retainer	1			
9	19400020810_02	Han HPR HPTC 850 CS-cover-insul.-body	1			
8	19400020810_01	Han HPR HPTC 850/1400 CS-HB-insul.-body	1			
7	19400020800_11	Han HPR HPTC 850 CS-Cover	1			
6	19000007127	Han CGM-M-Rail M40 D.26.5-32mm	1	46	50	20,0
5	19400020890_05	O-Ring	1			
4	19400020890_06	O-Ring	2			
3	743400	Lock washer	2			
2	742900	Hexagon socket head cap screw ISO 4762-M8x35	2	6	-	14,5
1	19400020808_50	Han HPR HPTC 850/1400 CS-HB-M40	1			
item	partnumber	partname	QTY	SW1	SW2	tightening torque Nm

parts in scope of delivery are not assembled
assembly instruction enclosed

crimp zone acc. to DIN EN 46235, indicator 25
for stranded fine wire acc to VDE 0295 class 5/ IEC 60228 class 5
wire gauge: 185mm²

Coating	A=	mm ²	V=	mm ³	m=	g	Mat.
	All Dimensions in mm Original Size DIN A3		Scale	Free size tol.		Ref.	
			1:2			Sub.	
	All rights reserved Department EL PD		Created by MEYERLE	Inspected by 00103912	Standardisation	Date 2021-10-04	State Final Release
HARTING D-32339 Espelkamp			Title Han HPR HPTC 850 CS UNSH IP65/67 185			Doc-Key / ECM-Nr. 100941851/UGD/002/E 500000203563	
			Type TB	Number 10 40 281 2128		Rev. E	Page 1/1