

TY125-40X



CABLE TIE 40LB 5.5IN UV BLACK NYLON



General Information

Extended Product Type	TY125-40X
Product ID	7TAG054360R0141
EAN	5414363060680
Catalog Description	CABLE TIE 40LB 5.5IN UV BLACK NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 141.48mm (5.57 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.17mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Bulk Pack

Ordering

EAN	5414363060680
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.001 lb .454 g
--------------------	-------------------

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	9 in 229 mm
Package Level 1 Height	2.6 in 66 mm
Package Level 1 Depth / Length	12.7 in 323 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	13.2 in 335 mm
Package Level 2 Height	10.5 in 267 mm
Package Level 2 Depth / Length	17.1 in 434 mm

Additional Information

Brand / Label	Ty-Fast
---------------	---------

Bundle Diameter	0.06 to 1.26 in 1.6 to 32 mm
Color	Black
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6 Weather Resistant
Product Name	PLASTIC CABLE TIE
Product Type	Intermediate
Special Functions	The integrally formed nylon pawl combines low insertion and high locking strength.
Standards	UL E49405
Tensile Strength	40 lb 180 N
Thickness	0.046 in 1.17 mm
UPC	786210898568

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY125-40X
Instructions and Manuals	TY125-40X

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

