



**MST single phase safety transformer**

P: 250VA IN: 208...550VAC OUT: 24VAC

Single-phase - Control and Isolation Transformers  
 250 VA  
 Isolation class T 40/B

Other voltages on request.

**Link to Product****Illustration**



Product may differ from Image

### Approvals



### Input

Input voltage	208, 230, 380, 400, 420, 440, 460, 480, 500, 525, 550 V AC
Input current	1.35 A (208 V AC); 0.51 A (550 V AC)
Inrush current	25 A (208 V AC); 9.3 A (550 V AC)
Short-circuit current	23 A (208 V AC); 8.7 A (550 V AC)
Frequency	50...60 Hz

### General data

Standards	(EN 61558-1), (EN 61558-2-6), (EN 62041 category 0)
Test isolation voltage	4 kV (prim./sec.)
Mounting method	Key-hole mounting
Dimensions H × W × D	98×120×134
Fixing centers a × b × c	74.4×90×5.8
Drill hole Ø	5.8×10
Temperature range	-20...+40 °C, no condensation

### Output

Output voltage	24 V AC
----------------	---------

### Commercial data

country of origin	CZ
customs tariff number	85043180
minimum order quantity	1