


3/8" 12-SIDED SOCKETS

Description

Chrome-vanadium steel. In accordance with DIN ISO 3124.



Characteristics

Ref.	EAN	Square drive adapter	Diameter mm	Length mm
880135	3660338335778	3/8	6	25
880136	3660338335785	3/8	7	25
880137	3660338335792	3/8	8	25
880138	3660338335808	3/8	9	25
880139	3660338335815	3/8	10	25
880140	3660338335822	3/8	11	25
880141	3660338335839	3/8	12	25
880142	3660338335846	3/8	13	25
880143	3660338335853	3/8	14	25
880144	3660338335860	3/8	15	25
880145	3660338335877	3/8	16	25
880146	3660338335884	3/8	17	25
880147	3660338335891	3/8	18	25
880148	3660338335907	3/8	19	28
880149	3660338335914	3/8	20	28
880150	3660338335921	3/8	22	32