



Order symbol: TPC 131007
Product nbr: 5824040
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074309563
EI. number:
Finland:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	130	95	65	Rating: Ingress Protection (EN 60529): IP65 Impact Resistance (EN 62262): IK07/IK08 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): 1 Flammability Rating: UL 746C 5" Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 12
inch:	5.1	3.7	2.6	
Materials:				Certificates: SGS Fimko
Material:	Polycarbonate			
Base colour:	RAL 7035 -light grey			
Cover screws material:	Polyamide			
Cover colour:	RAL 7035 -light grey			
Cover screws colour:	Grey			
Gasket material:	Polyurethane			
Temperatures:				
Temperature °C (short term):	-40 ... 120 °C			
Temperature °C (continuous):	-40 ... 80 °C			
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			
Accessories:				
FP 10674				

