4 Pole Metal Clad Enclosed Switch Disconnector





Approvals	CB. CE & SEMKO	
UL Standard	UL508	
International/European Standard	IEC & EN 60947-1 and 3	

DATA		Range	MCLB1004PSTB	MCLB1254PSTB	Units
Rated operational voltage Ue			•	•	
IEC & EN		Volts	690	690	V
UL		Volts	600	600	V
Main switch: Isolating voltage up to		Volts	750	750	V
Rated impulse withstand voltage Uimp		Volts	6	6	kV
Rated uninterrupted current lu		Amps	100	125	Α
Rated operational current le					
	AC-22A	Up to 690V	100	125	Α
IEC & EN	AC-21A	Up to 690V	100	125	Α
	AC-1	Up to 690V	100	125	Α
Rated operational power AC-23A	(50-60Hz)	'		,	
		230(240)V	45	55	kW
IEC & EN	3 Phase	400(415)V	55	75	kW
		690V	90	90	kW
Rated operational power AC-3 (5	0-60Hz)				
IEC & EN		230(240)V	37	45	kW
	3 Phase	400(415)V	45	55	kW
		690V	55	55	kW
UL Power Rating			-		
DOL	3 Phase	120V	7.5	7.5	hp
		240V	20	30	hp
		480V	30	40	hp
		600V	40	50	hp
	1 Phase	120V	3	3	hp
		240V	7.5	7.5	hp
UL Short Circuit Ratings					
Fuse rating, class J		Amps	125	125	Α
Fuse rating, class RK5		Amps	-	-	Α
Rated Fused short circuit current		Amps	10	10	kA
Short Circuit Capacity (IEC)					
Max fuse size (Type gl)		Amps	125	125	Α
Rated Fused short circuit current		Amps	30	30	kA

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




4 Pole Metal Clad Enclosed Switch Disconnector




DATA		MCLB1004PSTB	MCLB1254PSTB	Units			
Terminal Specification							
Single/ Multiple strand wire		2.5	2.5	Min-mm ²			
		50	50	Max-mm ²			
Fine strand with sleeve		4	4	Min-mm ²			
	50	50	Max-mm ²				
American wire gauge		1	1	AWG			
Recommended Tightening Torque		2.5	2.5	Nm			

Terminal Configurations



Enclosure Dimensions



Part Number Table

Description	Part Number	
4 Pole Metal Clad Enclosed Switch Disconnector, 100A	MCLB1004PSTB	
4 Pole Metal Clad Enclosed Switch Disconnector, 125A	MCLB1254PSTB	

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

