



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCMD XCKT XCKD XCKP

Associated body	ZCD37 ZCMD37L1 ZCP27 ZCT27G11 ZCMD21C12 ZCD35 ZCMD37L2 ZCMD21L2 ZCD31 ZCMD25L5 ZCT26N12 ZCMD81L2 ZCT28G11 ZCD28 ZCD27 ZCT21N12 ZCMD41L2 ZCD26 ZCMD37L5 ZCMD21M12 ZCT26P16 ZCP29M12 ZCMD41L1 ZCD29M12 ZCD21 ZCMD29L1 ZCMD29L5 ZCT21G11 ZCP21M12 ZCMD61C12 ZCMD81L5 ZCMD39L5 ZCT27N12 ZCT25G11 ZCMD29C12 ZCMD21L08U78 ZCMD25L2 ZCD39 ZCP26 ZCP29 ZCMD69C12 ZCP39 ZCP25 ZCT25N12 ZCMD25L1 ZCT28N12 ZCT27P16 ZCP35 ZCD25 ZCMD39L1 ZCD29 ZCT26G11 ZCD21M12 ZCMD21L1 ZCT21P16 ZCMD41L5 ZCP37 ZCP28 ZCMD21L08R12 ZCP21 ZCMD29L2 ZCT25P16 ZCMD81L1 ZCMD39L2 ZCMD61M12 ZCP31 ZCMD21L5 ZCT28P16
Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach, 1 direction

Complementary

Positive opening

With

Environment

Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Package weight(Lbs)	0.56 oz (16.000 g)
---------------------	--------------------

Packing Units

Package 1 Height	0.59 in (15.000 mm)
Package 1 width	0.98 in (25.000 mm)
Package 1 Length	1.18 in (30.000 mm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------