

Inset Trend 62 Flush

INSET TREND 62 FL ES50 WH EX-LMP
3083550



Product features

- 62mm cut out. Fixed. White bezel.



PRODUCT OVERVIEW

Product name	INSET TREND 62 FL ES50 WH EX-LMP
Technology	LED/Halogen
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number SE	7464262
Warranty	3 years
LOR (%)	Dependent on lamp
Light colour	N/A
Light source included	Fixture without Lightsource
Electrical protection	Class II
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	8711971835509

DATA TABLE

General data

Product name	INSET TREND 62 FL ES50 WH EX-LMP
Technology	LED/Halogen
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number SE	7464262
Warranty	3 years

Optical data

LOR (%)	Dependent on lamp
---------	-------------------

Inset Trend 62 Flush

INSET TREND 62 FL ES50 WH EX-LMP
3083550

Light colour	N/A
Adjustable chromaticity	N

Electrical data

Light source included	Fixture without Lightsource
Mains voltage (V)	220-240V
Electrical protection	Class II
Transformer required	No
Nominal Frequency (Hz)	50/60Hz

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	82
Nominal Product Width (mm)	82
Nominal Product Height (mm)	85
Cutout Dimensions (W x L in mm or Diameter in mm)	62
Weight (kg)	0.101
Recessed Depth (mm)	85

Packaging

Single packaging type	Carton
Product EAN number	8711971835509
Packaging single length / height (cm)	13.4
Packaging single width (cm)	10.1
Packaging single depth (cm)	7.0
DUN14 (outer)	18711971835506
Units per outer package	30
Packaging outer length / height (cm)	23.9
Packaging outer width (cm)	28.9
Packaging outer depth (cm)	53.1

TECHNICAL DRAWINGS

