

Compact manual hydraulic punch with overpressure valve

Straight



Application:

For punching holes with Tristar sheet metal punches.

Execution:

- Straight aluminium version
- Weighs just 1.6 kg
- 75 kN punching force
- Max. operating pressure: 650 bar
- Punching capacity: Round holes up to 82 mm/2 mm sheet metal, 64 mm/3 mm sheet metal
- Square hole punch up to 68 x 68 mm/2 mm sheet metal
- Square hole punch up to 46 x 86 mm/2 mm sheet metal
- Set comprising hydraulic punch, 19 and 19 x 9.5 mm tension bolt, HSS 11.0 mm drill for pre-drilling, 3-piece spacer sleeve set
- Set in robust and practical plastic case

Advantage:

- Tool service life is extended by the integrated overpressure valve with automatic pressure shutdown at 650 bar
- The practical manual punch, without hose and cylinder, is ideal for workshops and assembly tasks



Art. no.	53829 200
Brand	ALFRA
Manufacturer Part Number	02001
Design	Straight
Suitable for max. sheet metal thickness	3 mm
Gross Weight	3.300 kg
Product Group	554

EAN

4030266006580