

High Lux Xenon – Handpiece solution


Hybec P/N : HH38K1 (H1360)

Replacement for KaVo™ P/N : 553-3881 for
LCM Illumination System / Lux Coupler Fiber Optic




ADVANTAGES

- Brighter Output than Original Brand
- Higher Spot Intensity
- Excellent Uniform Brightness
- Longer Life and Performance Repeatability
- Competitive Price



SPECIFICATIONS



Voltage.....3.5V
Current.....740mA
MSCP.....3.20
Lumens.....40.2
Life.....70 hours (Ave.)




SPOT INTENSITY



High Lux Xenon



Call us for other Dental lamps.



Dental Lamp Supplies

Unit 9, Barrington Industrial Estate,
Leycroft Road, Leicester, LE4 1ET

Tel : +44-116-235-8818 Fax : +44-116-235-8810

E-mail : enquiries@hybec.com

Web ; www.dentallampsupplies.com