


Digital Hand-Tachometer
Tachymètre Numérique Portatif
Tachómetro digital manual
Tachimetro digitale a mano

N0000.9000A




1



2



3



MODE **4**

rpm m/min m/sec ft/min ft/sec in/min m ft in

rpm → m/min m/sec ft/min ft/sec in/min m ft in

8.8.8.8.8

1.00 - 99999 rpm

max 600 mm
24 in

A

MODE **5**

rpm m/min m/sec ft/min ft/sec in/min m ft in

rpm → m/min m/sec ft/min ft/sec in/min m ft in

8.8.8.8.8

0,10 - 19999 rpm

A

B

MODE **6**

rpm m/min m/sec ft/min ft/sec in/min m ft in

rpm → m/min m/sec ft/min ft/sec in/min m ft in

8.8.8.8.8

A

B

	0.1 m	6"	12"
m/min	0.10-1999	0.10-1524	0.40-609.6
ft/min	0.40-6550	0.40-5000	0.40-2000
in/min	4.00-78700	4.00-60000	4.00-24000
m/sec	0.10-33.30	0.10-25.40	0.10-10.16
ft/sec	0.10-109	0.10-83.33	0.10-33.33
m	0.00-99999	0.00-99999	0.00-99999
ft	0.00-99999	0.00-99999	0.00-99999
in	0.00-99999	0.00-99999	0.00-99999

MODE **7**

HANDLING

A


B


C


MEM

8


MEM ▶ MAX ▶ MIN ▶ AV ▶




 ± 0.02% ± 1 digit (for rpm)

 auto power off 30 sec (Data store)

 0° ... 50° C / 32° ... 122° F

 -20° ... 70° C / -4° ... 158° F

 approx. 40 h (alkaline Battery)

 2 x AA Alkaline or Rechargeable

CE



Caution