








PVC								
mm <sup>2</sup>	AWG	Grösse Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	L mm	øD mm	Werkzeuge Outils Toolings
0.5-1	22-18	6.3 x 0.8		3944s	*	21.5	1.7	3974n, 3983p.1, 3984c, 3984cx, 3984o, 3984ox, 3986c, 3986n, 3986s
1.5-2.5	16-14	6.3 x 0.8		3945s	*	22	2.3	
4-6	12-10	6.3 x 0.8		3947s	*	24	3.4	3974n, 3984o, 3986c, 3986n, 3986s







PA								
mm <sup>2</sup>	AWG	Grösse Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	L mm	øD mm	Werkzeuge Outils Toolings
0.5-1	22-18	6.3 x 0.8		3963s	*	21	1.7	3974n, 3983p.1, 3984c, 3984cx, 3984o, 3984ox, 3986c, 3986n, 3986s
1.5-2.5	16-14	6.3 x 0.8		3966s	*	22	2.3	
4-6	12-10	6.3 x 0.8		3967s	*	24	3.4	3974n, 3984o, 3986c, 3986n, 3986s


hitzeschrumpfend  
 UL-No. E235796



thermorétractable

heatshrinkable



PA / HDPE										
mm <sup>2</sup>	AWG	Grösse Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	L mm	A mm	øD mm	øD1 mm	Werkzeuge Outils Toolings
0.5-1	22-18	6.3 x 0.8		3963sh	*	36.5	6	1.6	6	3986f, 3986h, 3986t
1.5-2.5	16-14	6.3 x 0.8		3966sh	*	36.5	6	2.3	6	
4-6	12-10	6.3 x 0.8		3967sh	*	37	6	3.4	7	



PA									
mm <sup>2</sup>	AWG	Grösse Grandeur Size	Farbe Couleur Colour	Artikelnummer Numéro d'article Part-No.	DIN	L mm	A mm	øD mm	Werkzeuge Outils Toolings
0.5-1	22-18	6.3 x 0.8		3937s	*	15	16	1.7	3984cwx, 3994
1.5-2.5	16-14	6.3 x 0.8		3939s	*	15	17	2.3	