


EBC007



Splitter box

ZDO6H050MSS0000-00STAK190MSS



Application	
Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes
Electrical data	
Operating voltage [V]	< 30 AC/DC; ("supply class 2" to cULus)
Max. current load per module/slot [A]	4
Max. current load total [A]	12



Splitter box

ZDO6H050MSS0000-00STAK190MSS

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67; ("enclosure type 1" according to cULus)

Mechanical data

Weight [g]	252.5
Materials	PA
Number of ports splitter box	6
Connector type	M12

Accessories


Accessories (supplied)	Protective caps: 2 labels: 6
------------------------	---------------------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - Connection

Connector: 1 x M23; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm



Connection

+ 19	1 (1...6)	C
- 6	3 (1...6)	C
± 12	5 (1...6)	C
15	4 (1)	C
7	2 (1)	C
5	4 (2)	C
4	2 (2)	C
16	4 (3)	C
8	2 (3)	C
3	4 (4)	C
14	2 (4)	C
17	4 (5)	C
9	2 (5)	C
2	4 (6)	C
13	2 (6)	C

EBC007



Splitter box

ZDO6H050MSS0000-00STAK190MSS

Electrical connection - slot

Connector: 6 x M12; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

