



Figure similar

PM-D F PROFISAFE POWER MODULE FOR FAILSAFE MOTOR STARTER, FOR FAILSAFE CONTACT MULTI-PLIER, W. 6 TRIPPING GROUPS FOR PROFIBUS OR PROFINET PLUGABLE ONTO TM-PF30 S47-F1 FOR F-FREQUENCY CONVERTERS 30MM

General technical data:

product brand name		Safety Module PROFIsafe
Product designation		PM-D F PROFISAFE
Protection class IP		IP20
Product function		Yes
• Bus communication		No
• Short circuit protection		
Operating current at 400 V Rated value	A	6
SIL Claim Limit (subsystem) acc. to EN 62061		3
Category acc. to EN ISO 13849-1		4




Control circuit/ Control:


Type of voltage of the control supply voltage		DC
Control supply voltage for DC		
• Rated value	V	24
• Rated value	V	26.4 ... 21.6

Installation/ mounting/ dimensions:

Width	mm	30
Height	mm	196.5
Depth	mm	117.5

Certificates/ approvals:

General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity
 GOST		Type Examination Certificate Type Examination other
		 EG-Konf.

Shipping Approval	other
 GL	Confirmation Environmental Confirmations Declaration of Conformity

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RK19033BA02>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RK19033BA02/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK19033BA02&lang=en>



3RK1903-3BA02_ALL

last modified:

15.01.2015