

Socket sets and sockets

12,5
1/2"

DIN
3120

ISO
1174-1

TCS 52/17



TCS



- 175 x 350 x 40 mm
- 17 pieces

Code

g

96838177


1605

No	Content
52	1/2" Ø 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24; 27; 30; 32 mm

TCS 52/18MF



TCS



- 175 x 350 x 55 mm
- 18 pieces

Code

g

96830359

1850

No	Content
52	1/2" Ø 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24; 27; 30; 32; 34 mm

TCS 50/51/52/32



TCS



- 175 x 350 x 50 mm
- 32 pieces

Code

g

96838191

2950

No	Content
50	1/2" Ø 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 30 mm
51	1/2" Ø 22; 27 mm
52	1/2" Ø 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24; 27; 30; 32 mm

TCS 50a/17



TCS



- 175 x 350 x 40 mm
- 17 pieces

Code

g

96838780

1685


No	Content
50a	1/2" Ø 3/8; 7/16; 1/2; 9/16; 19/32; 5/8; 11/16; 3/4; 25/32; 13/16; 7/8; 15/16; 1; 1 1/16; 1 1/8; 1 3/16; 1 1/4"

51

○ Sockets

AS HPQ

- extra deep
- DIN 3124/ISO 2725-1, E DIN EN 3710, E DIN EN 3709, ASME B 107.5M
- HPQ® high performance steel, chrome plated



Code	Ø mm/"	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	g	g	g
03020010	10	14.5	22	9	83	19	67	90	10	10
03020013	13	18.3	22	12	83	35	67	122	10	10
03020014	14	19.9	22.7	13	83	35	65.2	129	10	10
03020015	15	21.2	22.7	14	83	35	64.9	125	10	10
03020016	16	22.4	23.7	15	83	35	64.6	145	10	10
03020216	16-5/8 ¹⁾	22.4	23.7	15.4	83	19	64.5	137	10	10
03020017	17	24	23.7	16	83	35	64.3	145	10	10
03020018	18	24.7	23.7	17	83	35	64.1	170	10	10
03020019	19	26.2	25	18	83	35	66.7	165	10	10
03020208	20.8-13/16 ¹⁾	27.7	26	20	83	22	66.2	194	10	10
03020021	21	28.7	26.5	20	83	35	66.2	231	10	10
03020022	22	29.7	27.5	21	83	35	65.5	200	10	10
03020024	24	32	30	21	83	35	66.1	251	5	5
03020026	26	34.4	32.5	23	83	35	65.3	334	5	5
03020027	27 ²⁾	36.2	34	27	83	20	60	280	5	5
03020030	30 ²⁾	39.7	37.5	30.2	83	35	65	341	5	5
03020032	32	42.4	40	29	83	35	63.9	435	5	5

¹⁾ with rubber insert for spark plugs

²⁾ for diesel injector (Audi, Daihatsu, Ford, Mazda, Mercedes, Mitsubishi, Nissan, Opel, Peugeot, Toyota, VW, Volvo)

51a

○ Sockets

AS HPQ

- extra deep
- ASME B 107.1, Fed. Spec. GGG-W-641, SAE AS 954-E
- HPQ® high performance steel, chrome plated

Code	Ø "	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	g	g	g
03420024	3/8	14.3	22	8.3	83	19	67	93	5	5
03420028	7/16	16.3	22	9.9	83	19	67	102	5	5
03420032	1/2	18.3	22	11.5	83	35	67	122	5	5
03420034	9/16	20.3	22.7	13.1	83	35	65.2	131	5	5
03420036	5/8	22.4	23.7	15	83	35	64.6	135	5	5
03420038	11/16	24.2	23.7	16.5	83	35	64.2	158	5	5
03420040	3/4	26.2	25	18	83	35	66.7	188	5	5
03420042	13/16	27.7	26	19.5	83	35	66.3	170	5	5
03420044	7/8	29.7	27.5	21	83	35	65.9	200	5	5
03420046	15/16	32	30	22.6	83	35	65.7	281	5	5
03420048	1	33.7	32	24.2	83	35	65	260	5	5
03420050	1 1/16	36.2	34	25.8	83	35	64.5	359	5	5
03420052	1 1/8	38.1	36	27.4	83	35	64	300	5	5
03420054	1 3/16	39	37	28	83	35	63.9	377	5	5
03420056	1 1/4	40	38	30.5	83	35	63.1	340	5	5
03420058	1 5/16	41.8	40	32.1	83	35	62.7	375	5	5
03420060	1 3/8	46	44	33.7	83	35	62.2	506	5	5
03420062	1 7/16	49.4	47	34	83	35	62.1	635	5	5
03420064	1 1/2	51	49	35	83	35	61.8	675	5	5

5100

Rubber insert

- for 20.8 mm (No 46; 51; 51S)

Code	g	g
09010001	6	5