


## P2664

### Pylon Probe

Product Family: Pylon



#### Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 2.00 (57.00) - 3.60 (102.00) - Stainless Steel

Alternate - 3.00 (85.00) - 5.70 (162.00) - Stainless Steel

#### Body Type

Straight

Pylon Bend

#### Additional information:

Use ARIT25 tool for installation

#### Mechanical:

**Test Center (mil):** 100

**Test Center (mm):** 2.54

**Overall Length (mil):** 895

**Overall Length (mm):** 22.73

**Overall Length Remark:** Tip 1C: 845 mil (21.46 mm)

Tip 2R: 935 mil (23.75 mm)

**Full Travel (mil):** 114

**Full Travel (mm):** 2.90

**Recommended Travel (mil):** 84

**Recommended Travel (mm):** 2.13

#### Thermal:

**Max Operating Temp (°C):** 150

**Min Operating Temp (°C):** -55

#### Electrical:

**Current Rating (Amps):** 5

**Average DC Resistance lower than (mOhm):** 10

#### Materials & Finishes:

**Plunger Material:** Heat-treated BeCu, Gold plated over hard Nickel

**Barrel Material:** Phosphor Bronze, Gold plated


**Ball Material:** Stainless Steel

**TIPS:**

Tip Materials: BeCu, Gold plated

**Tips:**


P2664-1C




P2664-1R




P2664-1W



P2664-2R




P2664-4V




**Related Products:**


PR541-0




PR541-0F




PR541-1




PR541-1F




PR541-2




PR541-2F



PR541-3



PR541-3F



ARIT-25

