



Mallory Sonalert Products, Inc.

Part #: **SCE016XD2DB1S**

Sales Outline Drawing


Revision: **A**

Specifications:

| | | | | |
|------------------------|--|-----------------------------|-------------------------------|------------------------------|
| Sound Level Category: | Extra Loud | Loud | Extra Loud | Loud |
| Mode of Operation: | Continuous | Continuous | Fast Pulse | Fast Pulse |
| Pulse Rate (PPS): | N/A | N/A | 10 | 10 |
| Loudness @ 2 FT: | 95 to 105 dB(A) Typ. | 85 to 95 dB(A) Typ. | 95 to 105 dB(A) Typ. | 85 to 95 dB(A) Typ. |
| Frequency: | 2000 ± 500 Hz | 2000 ± 500 Hz | 2000 ± 500 Hz | 2000 ± 500 Hz |
| Connection: | TERMINALS ONLY | TERMINALS; BLUE WIRE TO (-) | TERMINALS; YELLOW WIRE TO (-) | TERMINALS; BOTH WIRES TO (-) |
| Voltage Rating: | 6 to 16 VDC | | | |
| Current Draw: | 40mA MAX | | | |
| Housing Material: | 6/6 Nylon, Color: Black | | | |
| Storage Temperature: | -40° to +85° C | | | |
| Operating Temperature: | -40° to +85° C | | | |
| Panel Mounting: | Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. | | | |
| Knurled Nut: | Used to attach part to panel. The max recommended torque is 10 in-lbs. | | | |
| Weight (Typical): | 2.1 oz (60g) | | | |
| NEMA 3R,4X, & 12: | Approved with use of ACC03. | | | |
| cUL Recognition: | cUL Recognized | | | |
| Options: | Please contact factory. | | | |

Dimensions: Inches (mm)

ROHS Compliant



NOTE A: TERMINALS-.032 BRASS TIN PLATED, TAPPED FOR #6-32 SCREW. TWO #6-32 NICKEL PLATED BRASS SCREWS INCLUDED. WILL ACCEPT 1/4" QUICK CONNECT.

NOTE B: MOUNTING- REMOVE BLACK PLASTIC NUT AND INSERT THREADED FRONT THROUGH 1.25" HOLE PUNCHED IN PANEL, IF ORIENTATION IS NEEDED, NOTE LOCKING FLATS ON DRAWING. SCREW NUT BACK ON. DO NOT OVERTIGHTEN.