

## Product information

# 83 10 030

## Pipe Wrench 90°

DIN 5234

- Swedish pattern
- 90° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



| General         |                       |
|-----------------|-----------------------|
| Article No.     | 83 10 030             |
| EAN             | 4003773022329         |
| Pliers          | red powder-coated     |
| Weight          | 3,433 g               |
| Dimensions      | 650 x 96 x 25 mm      |
| Standard        | DIN 5234              |
| REACH compliant | does not contain SVHC |
| RoHS compliant  | not applicable        |

| Technical details               |          |
|---------------------------------|----------|
| Clamping width                  | 110 mm   |
| Capacities for pipes (diameter) | Ø 4 3/8  |
| Capacities for pipes (diameter) | Ø 110 mm |
| Capacities for nuts             | 105 mm   |
| Inner diameter, inches          | Ø 3 Inch |

technical change and errors excepted

