

PRODUCT-DETAILS

# SP20/BL/10M

## 10M X SP20/BLACK CONDUIT



### General Information

Extended Product Type	SP20/BL/10M
Product ID	7TCA296020R0133
EAN	5020963000041
Catalog Description	10M X SP20/BLACK CONDUIT
Long Description	Liquid Resistant, General Purpose, Highly Flexible Conduit, Nominal Conduit Size 20mm, Outside Diameter 21.5mm, Inside Diameter 16.9mm, Static Bend Radius 45mm, Reel Length 10 Meters, PVC Jacket with Galvanised Steel Core, Black

### Ordering

EAN	5020963000041
Customs Tariff Number	8307106000

### Dimensions

Product Net Weight	6.75 lb 3.061 kg
--------------------	---------------------

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	17 in 432 mm

Package Level 2 Height	16 in 406 mm
Package Level 2 Depth / Length	16 in 406 mm

---

### Additional Information

Application	Indoors / Outdoors - Light Industrial, General Purpose, Buildings
Brand / Label	Adaptaflex
Color	Black
Flexibility	High
Inside Diameter	16.9 mm
Material	Galvanized Steel Core with PVC Jacket
Nominal Size	1/2 in
Number of Batteries	0
Outside Diameter	21.5 mm
Product Name	ADAPTAFLEX
Product Type	High Flexibility Conduit
Radius	45 mm
UPC	786210259239

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SP20/BL/10M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SP20/BL/10M

---

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

