

Permanent NEO lifting magnet

3-fold safety

Application:

For the secure lifting of sheet metals, profiles, panels, round- and bar-shaped parts or for loading and unloading machines.

Advantage:

- Large lifting capacity with low tare weight and small dimensions
- Robust, low-maintenance, user-friendly
- Easy to switch on and off using the hand lever, with safety lock

Delivery:

With test certificate



Art. no.	77301 015
Load-carrying capacity	600 kg
Load-carrying capacity for round materials	300 kg
Tear-off weight certified	1900 kg
For min./max. round material diameter	65-270 mm
Suitable for min. sheet metal thickness	6 mm
Surface area length	246 mm
Surface area width	120 mm
Height up to load hook	164 mm
Colour	Orange

EAN-Code

0705632164440