


# SS Radial Miniatur

## Elektrische Daten:

Betriebsspannung:	6,3 - 63V
Temperaturbereich:	-40 - +105°C
Lebensdauer:	1000 Stunden bei 105°C
Kapazitätsbereich:	0,1 - 100 µF
Kapazitätstoleranz:	20%
DC Verluststrom:	0,01 CV (µA) or 3 µA

Verlustfaktor: (120 Hz, 25°C)

WV (V)	6,3	10	16	25	35	50	63
DF (%)	24	20	17	15	12	10	8



Gehäusegröße D x H

Kapazität/ Volt							
µF/ V	6,3	10	16	25	35	50	63
0,1						4x7	4x7
0,22						4x7	4x7
0,33						4x7	4x7
0,47						4x7	4x7
0,68						4x7	
1						4x7	4x7
2,2			4x7			4x7	4x7
3,3			4x7			4x7	4x7
4,7			4x7	4x7	4x7	4x7	4x7
4,7					5x7	5x7	6x7
10			4x7	4x7	4x7	4x7	5x7
10				5x7	5x7	5x7	6x7
10				6x7		6x7	
22	4x7	4x7	4x7	4x7	5x7	6x7	
22		5x7	5x7	5x7	6x7		
22				6x7			
33	5x7	4x7	4x7	5x7	6x7		
33		5x7	5x7	6x7			
47	4x7	4x7	5x7	5x7	6x7		
47	5x7	5x7	6x7	6x7			
47		6x7					
68			5x7				
100	5x7	5x7	5x7	6x7			
100	6x7	6x7	6x7	8x7			
150			6x7				
220	6x7	6x7	8x7				
220			8x9				
330	8x7		8x9				
470		8x9					

Rastermaß:

D	4	5	6
Rm	1,5	2	2,5
d	0,45	0,45	0,45