

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

MATERIAL

Polyethylene (PE), RAL 9005 (C9) black colour or RAL 7042 (C34) grey colour, satin finish.

STANDARD EXECUTIONS


- **NIL.Q:** for square tubes.
- **NIL.R:** for rectangular tubes.
- **NIL.T:** for round tubes.

FITTING

Their fitting to the round, square or rectangular section tube or profile ends can be made either by hand or by a mallet.

SPECIAL EXECUTIONS ON REQUEST

RAL 9003 white coloured inserts.



* Complete with colour index, example: 435210-C9 NIL.Q-10-C9




NIL.Q

| Code | Description | B | h | h1 | Tube external diameter | Tube thickness |
|----------|-------------|----|------|----|------------------------|----------------|
| 435210-* | NIL.Q-10-* | 10 | 12 | 4 | 10 | 0,8+2,5 |
| 435212-* | NIL.Q-12-* | 12 | 12 | 4 | 12 | 1+2 |
| 435213-* | NIL.Q-13-* | 13 | 12 | 4 | 13 | 0,5+2 |
| 435215-* | NIL.Q-15-* | 15 | 11,5 | 3 | 15 | 1+2 |
| 435216-* | NIL.Q-16-* | 16 | 11,5 | 5 | 16 | 1+2,5 |
| 435218-* | NIL.Q-18-* | 18 | 11,5 | 5 | 18 | 1,5+3 |
| 435220-* | NIL.Q-20-* | 20 | 11,5 | 5 | 20 | 1+3 |
| 435222-* | NIL.Q-22-* | 22 | 12 | 5 | 22 | 1+3,5 |
| 435225-* | NIL.Q-25-* | 25 | 11,5 | 5 | 25 | 1+3 |
| 435228-* | NIL.Q-28-* | 28 | 11,5 | 5 | 28 | 1+3 |
| 435230-* | NIL.Q-30-* | 30 | 11,5 | 5 | 30 | 1+3 |
| 435232-* | NIL.Q-32-* | 32 | 11,5 | 5 | 32 | 1+3,5 |
| 435234-* | NIL.Q-34-* | 34 | 14,5 | 5 | 34 | 1+3 |
| 435235-* | NIL.Q-35-* | 35 | 11,5 | 5 | 35 | 1+3 |
| 435238-* | NIL.Q-38-* | 38 | 14,5 | 5 | 38 | 1+3,5 |
| 435240-* | NIL.Q-40-* | 40 | 14,5 | 5 | 40 | 1+3 |
| 435245-* | NIL.Q-45-* | 45 | 14,5 | 5 | 45 | 1+3 |

NIL.Q

| Code | Description | B | h | h1 | Tube external diameter | Tube thickness |
|----------|----------------|------|------|-----|------------------------|----------------|
| 435250-* | NIL.Q-50-* | 50 | 14,5 | 5 | 50 | 1+2,5 |
| 435370-* | NIL.Q-50-2.6-* | 50 | 24 | 5,5 | 50 | 2.6+4 |
| 435255-* | NIL.Q-55-* | 55 | 14,5 | 5 | 55 | 2+4,5 |
| 435260-* | NIL.Q-60-* | 60 | 15 | 5 | 60 | 1,5+3,5 |
| 435265-* | NIL.Q-65-* | 65 | 21 | 5 | 65 | 1+3 |
| 435270-* | NIL.Q-70-* | 70 | 22 | 5 | 70 | 2+5 |
| 435275-* | NIL.Q-75-* | 75 | 21 | 6 | 75 | 2+4,5 |
| 435276-* | NIL.Q-76,2-* | 76,2 | 21 | 6 | 76,2 | 2,5+5 |
| 435280-* | NIL.Q-80-* | 80 | 21 | 6 | 80 | 1,5+4 |
| 435290-* | NIL.Q-90-* | 90 | 21 | 6 | 90 | 3+5 |
| 435295-* | NIL.Q-95-* | 95 | 21,5 | 6 | 95 | 3,5+5,5 |
| 435300-* | NIL.Q-100-* | 100 | 21 | 7 | 100 | 1+4 |
| 435310-* | NIL.Q-110-* | 110 | 24 | 6 | 110 | 3+5 |
| 435320-* | NIL.Q-120-* | 120 | 30 | 5 | 120 | 2,5+6 |
| 435340-* | NIL.Q-140-* | 140 | 34 | 3 | 140 | 4+7 |
| 435350-* | NIL.Q-150-* | 150 | 28 | 7 | 150 | 5+8 |



* Complete with colour index, example: 435410-C9 NIL.R-20x10-C9

C9 RAL9005 **C34** RAL7042

NIL.R

| Code | Description | B | L | h | h1 | Tube external diameter | Tube thickness |
|---------|--------------|----|----|------|-----|------------------------|----------------|
| 435410* | NIL.R-20x10* | 20 | 10 | 12 | 3 | 20x10 | 0,8+2 |
| 435411* | NIL.R-20x15* | 20 | 15 | 11.5 | 5 | 20x15 | 1+2 |
| 435430* | NIL.R-25x10* | 25 | 10 | 11.5 | 3 | 25x10 | 0,8+2 |
| 435431* | NIL.R-25x15* | 25 | 15 | 11.5 | 5 | 25x15 | 1+2,5 |
| 435432* | NIL.R-25x20* | 25 | 20 | 11.5 | 5 | 25x20 | 1+3 |
| 435450* | NIL.R-30x10* | 30 | 10 | 11.5 | 3 | 30x10 | 1+2 |
| 435451* | NIL.R-30x15* | 30 | 15 | 11.5 | 5 | 30x15 | 1+2,5 |
| 435452* | NIL.R-30x20* | 30 | 20 | 11.5 | 5 | 30x20 | 1+3 |
| 435470* | NIL.R-35x10* | 35 | 10 | 11.5 | 3.5 | 35x10 | 1+2 |
| 435471* | NIL.R-35x20* | 35 | 20 | 11.5 | 5 | 35x20 | 1+2,5 |
| 435472* | NIL.R-35x25* | 35 | 25 | 11.5 | 5 | 35x25 | 1+3 |
| 435490* | NIL.R-40x15* | 40 | 15 | 12 | 5 | 40x15 | 1+2 |
| 435491* | NIL.R-40x20* | 40 | 20 | 12 | 5 | 40x20 | 1+3 |
| 435492* | NIL.R-40x25* | 40 | 25 | 11.5 | 5 | 40x25 | 1+3 |
| 435493* | NIL.R-40x30* | 40 | 30 | 11 | 5 | 40x30 | 1+3 |
| 435494* | NIL.R-40x35* | 40 | 35 | 12 | 5 | 40x35 | 1+3 |
| 435510* | NIL.R-45x15* | 45 | 15 | 11 | 5 | 45x15 | 1,5+2 |
| 435511* | NIL.R-45x20* | 45 | 20 | 11.5 | 5 | 45x20 | 1+3 |
| 435512* | NIL.R-45x25* | 45 | 25 | 12 | 5 | 45x25 | 1+3 |
| 435513* | NIL.R-45x30* | 45 | 30 | 12 | 5 | 45x30 | 1+2,5 |
| 435514* | NIL.R-45x35* | 45 | 35 | 12 | 5 | 45x35 | 1+3,5 |
| 435530* | NIL.R-50x20* | 50 | 20 | 15 | 5 | 50x20 | 1+3 |
| 435531* | NIL.R-50x25* | 50 | 25 | 11.5 | 5 | 50x25 | 1+3 |
| 435532* | NIL.R-50x30* | 50 | 30 | 12 | 5 | 50x30 | 1+3 |
| 435533* | NIL.R-50x35* | 50 | 35 | 14.5 | 5 | 50x35 | 1+3,5 |


NIL.R

| Code | Description | B | L | h | h1 | Tube external diameter | Tube thickness |
|---------|---------------|-----|----|------|----|------------------------|----------------|
| 435534* | NIL.R-50x40* | 50 | 40 | 15 | 5 | 50x40 | 1,5+3 |
| 435550* | NIL.R-60x20* | 60 | 20 | 14.5 | 5 | 60x20 | 1+3 |
| 435551* | NIL.R-60x25* | 60 | 25 | 15 | 5 | 60x25 | 1+3 |
| 435552* | NIL.R-60x30* | 60 | 30 | 15 | 5 | 60x30 | 1+2,5 |
| 435553* | NIL.R-60x35* | 60 | 35 | 15 | 5 | 60x35 | 1,5+3,5 |
| 435554* | NIL.R-60x40* | 60 | 40 | 14 | 5 | 60x40 | 1+3 |
| 435555* | NIL.R-60x45* | 60 | 45 | 15 | 5 | 60x45 | 1,5+4 |
| 435556* | NIL.R-60x50* | 60 | 50 | 14.5 | 5 | 60x50 | 1,5+3,5 |
| 435570* | NIL.R-70x20* | 70 | 20 | 19 | 5 | 70x20 | 1+3,5 |
| 435571* | NIL.R-70x25* | 70 | 25 | 18 | 5 | 70x25 | 1,5+2,5 |
| 435572* | NIL.R-70x30* | 70 | 30 | 15 | 5 | 70x30 | 1+3 |
| 435573* | NIL.R-70x35* | 70 | 35 | 15 | 5 | 70x35 | 1,5+3,5 |
| 435574* | NIL.R-70x40* | 70 | 40 | 20 | 5 | 70x40 | 1,5+3 |
| 435590* | NIL.R-80x20* | 80 | 20 | 18 | 5 | 80x20 | 1+3 |
| 435591* | NIL.R-80x30* | 80 | 30 | 14.5 | 5 | 80x30 | 1+2,5 |
| 435592* | NIL.R-80x40* | 80 | 40 | 14.5 | 5 | 80x40 | 1+3 |
| 435593* | NIL.R-80x50* | 80 | 50 | 22 | 5 | 80x50 | 1,5+4 |
| 435594* | NIL.R-80x60* | 80 | 60 | 25 | 5 | 80x60 | 1,5+3,5 |
| 435610* | NIL.R-90x20* | 90 | 20 | 14.5 | 5 | 90x20 | 1+2,5 |
| 435611* | NIL.R-90x40* | 90 | 40 | 15 | 5 | 90x40 | 2+4 |
| 435612* | NIL.R-90x50* | 90 | 50 | 22 | 5 | 90x50 | 2+4,5 |
| 435630* | NIL.R-100x30* | 100 | 30 | 15 | 5 | 100x30 | 1,5+3,5 |
| 435631* | NIL.R-100x40* | 100 | 40 | 14.5 | 5 | 100x40 | 1,5+4 |
| 435632* | NIL.R-100x50* | 100 | 50 | 24 | 5 | 100x50 | 1,5+4,5 |
| 435633* | NIL.R-100x60* | 100 | 60 | 25 | 6 | 100x60 | 1,5+4,5 |



Leveling feet and supports

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18



* Complete with colour index, example: 435010-C9 NIL.T-10-C9

C9
RAL9005

C34
RAL7042

NIL.T

| Code | Description | D | h | h1 | Tube external diameter | Tube thickness |
|----------|-------------|----|------|-----|------------------------|----------------|
| 435010.* | NIL.T-10.* | 10 | 11 | 3.5 | 10 | 1+2 |
| 435012.* | NIL.T-12.* | 12 | 11 | 3.5 | 12 | 1+2 |
| 435013.* | NIL.T-13.* | 13 | 11 | 4 | 13 | 1+2 |
| 435014.* | NIL.T-14.* | 14 | 11.5 | 5 | 14 | 1+2 |
| 435015.* | NIL.T-15.* | 15 | 11.5 | 3 | 15 | 1+2 |
| 435016.* | NIL.T-16.* | 16 | 11 | 5 | 16 | 1+2 |
| 435018.* | NIL.T-18.* | 18 | 11.5 | 5 | 18 | 1+2 |
| 435019.* | NIL.T-19.* | 19 | 11.5 | 5 | 19 | 1+2,5 |
| 435020.* | NIL.T-20.* | 20 | 11.5 | 5 | 20 | 1+2,5 |
| 435022.* | NIL.T-22.* | 22 | 11.5 | 5 | 22 | 1+2 |
| 435023.* | NIL.T-23.* | 23 | 11.5 | 5 | 23 | 1+2,5 |
| 435024.* | NIL.T-24.* | 24 | 11.5 | 5 | 24 | 1+2,5 |
| 435025.* | NIL.T-25.* | 25 | 11.5 | 5 | 25 | 1+3 |
| 435026.* | NIL.T-26.* | 26 | 11.5 | 5 | 26 | 1+3 |
| 435027.* | NIL.T-27.* | 27 | 11.5 | 5 | 27 | 1+3 |
| 435028.* | NIL.T-28.* | 28 | 11.5 | 5 | 28 | 1+3 |
| 435030.* | NIL.T-30.* | 30 | 11.5 | 5 | 30 | 1+2,5 |
| 435032.* | NIL.T-32.* | 32 | 12 | 5 | 32 | 1+3 |
| 435034.* | NIL.T-34.* | 34 | 11.5 | 5 | 34 | 1+3 |
| 435035.* | NIL.T-35.* | 35 | 11.5 | 5 | 35 | 1+3 |
| 435036.* | NIL.T-36.* | 36 | 11.5 | 5 | 36 | 1+3 |
| 435037.* | NIL.T-37.* | 37 | 11.5 | 5 | 37 | 1+3 |
| 435038.* | NIL.T-38.* | 38 | 11.5 | 5 | 38 | 1+3,5 |

NIL.T

| Code | Description | D | h | h1 | Tube external diameter | Tube thickness |
|----------|----------------|-----|------|----|------------------------|----------------|
| 435040.* | NIL.T-40.* | 40 | 11.5 | 5 | 40 | 1+3 |
| 435042.* | NIL.T-42.* | 42 | 11.5 | 5 | 42 | 1+3 |
| 435045.* | NIL.T-45.* | 45 | 11 | 5 | 45 | 1+3 |
| 435046.* | NIL.T-46.* | 46 | 11.5 | 5 | 46 | 1,5+3,5 |
| 435048.* | NIL.T-48.* | 48 | 11.5 | 5 | 48 | 1,2+3,6 |
| 435050.* | NIL.T-50.* | 50 | 14.5 | 5 | 50 | 1+2,5 |
| 435150.* | NIL.T-50-2.5.* | 50 | 11.5 | 5 | 50 | 2,5+4,5 |
| 435052.* | NIL.T-52.* | 52 | 14.5 | 5 | 52 | 1,5+3,5 |
| 435055.* | NIL.T-55.* | 55 | 11.5 | 5 | 55 | 1+3 |
| 435155.* | NIL.T-55-3.* | 55 | 14.5 | 5 | 55 | 3+5 |
| 435060.* | NIL.T-60.* | 60 | 14.5 | 5 | 60 | 1,5+3 |
| 435160.* | NIL.T-60-3.* | 60 | 17.5 | 5 | 60 | 3+5 |
| 435065.* | NIL.T-65.* | 65 | 14.5 | 5 | 65 | 1,5+3,5 |
| 435070.* | NIL.T-70.* | 70 | 21 | 5 | 70 | 1,5+3,5 |
| 435075.* | NIL.T-75.* | 75 | 21.5 | 6 | 75 | 1+3,5 |
| 435076.* | NIL.T-76.* | 76 | 21.5 | 6 | 76 | 1,6+4 |
| 435080.* | NIL.T-80.* | 80 | 22 | 5 | 80 | 1,5+3 |
| 435085.* | NIL.T-85.* | 85 | 21 | 6 | 85 | 1,5+4 |
| 435088.* | NIL.T-88.* | 88 | 21.5 | 6 | 88 | 1,5+4 |
| 435090.* | NIL.T-90.* | 90 | 21 | 6 | 90 | 1,5+5 |
| 435095.* | NIL.T-95.* | 95 | 21 | 6 | 95 | 1,5+4 |
| 435110.* | NIL.T-100.* | 100 | 28.5 | 6 | 100 | 2+4,5 |

Levelling feet and supports