

ROOF MOUNTED FAN AIR FLOW FREE AIR 405 M3
 PER H CUT OUT 345X265 MM 230 V AC RAL 7035
 INPUT POWER 40W DEGREE OF PROTECTION IP 44



Figure similar

Model		
product brand name		SIVACON
Product designation		Roof fans
Type of ventilation		ventilation
Fan design / Insertable fan		No
Design of the product / EMC version		No
General technical data		
A-rated sound power level / maximum	dB	62
Active power consumption / Rated value	W	40
Cutout width	mm	345
Cutout height	mm	265
Operating period	h	40 000
Operating temperature / minimum	°C	-10
Rotor speed / at 50 Hz / Rated value	1/min	1 430
Rotor speed / at 60 Hz / Rated value	1/min	1 700
Protection class		
Protection class IP		IP54
Electricity		
Consumed current / minimum	A	0.2
Main circuit		
Operating voltage		
• with AC / at 50 Hz / Rated value / maximum	V	230
• with AC / at 60 Hz / Rated value / maximum	V	230

Appearance		
Color		RAL 7035
Product details		
Product component / Fan		Yes
Number		
Number of ventilators		1
Mechanical Design		
Height	mm	340
Width	mm	420
Depth	mm	108
Installation location		Control cabinet roof
Mounting type		screw fixing
Mounting type		
• 19-inch installation		No
• wall mounting		No
Material		plastic
Certificates		
Equipment marking		
• acc. to DIN EN 61346-2		E
• acc. to DIN EN 81346-2		E
General Product Approval		



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR63235DL40>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR63235DL40/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR63235DL40

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015