


Artikelnummer/Itemnumber: 40103F

Edelstahlpfosten Ø 102 mm, herausnehmbar, selbsteinrastende Verriegelung mit feuerverzinkter Bodenhülse Typ 470.10, mit Dreikantverschluss nach DIN 3223, ohne Öse

Stainless steel post Ø 102 mm, removable, self-engaging lock with hot-dip galvanized ground socket part-no. 470.10, with triangular locking mechanism acc. with DIN 3223, without eyelet



Artikelbeschreibung:

Edelstahlpfosten Ø 102 mm Überflur ca. 900 mm geschliffen, herausnehmbar, selbsteinrastende Verriegelung mit feuerverzinkter Bodenhülse Typ 470.10, mit Dreikantverschluss nach DIN 3223, ohne Öse

Verwendungszweck:

Zum Sperren, Sichern und Schützen von Bereichen.

Technische Daten:

Gewicht: 12,00 kg/St
Material:
Edelstahl

item description:

Stainless steel post Above ground approx. 900 mm Ø 102 mm Ground, removable, self-engaging lock with hot-dip galvanized ground socket part-no. 470.10, with triangular locking mechanism acc. with DIN 3223, without eyelet

designated purpose:

For stopping, and securing or saving of areas.

technical specifications:

weight: 12,00 kg/pc
material:
stainless steel