

TA342912



Sample image

Order symbol : TA342912

Product nr : 5814004

Description : Enclosure, ABS



Remarks : Grey cover

EAN : 6418074060761

El. number :

- Finland : 3435690
- Denmark : 8212035085
- Sweden : 5814004

Including : Base with PUR gasket and screws for mounting plate/DIN-rail. cover with polyamide cover screws and plastic hinges.



2xM20 knock out

Dimensions :

| | Height | Width | Depth |
|--------|--------|-------|-------|
| mm : | 344 | 289 | 117 |
| inch : | 13.54 | 11.38 | 4.61 |

Materials :

Material : ABS

Temperatures :

| | |
|-------------------------------|-------------|
| Temperature °C (short term) : | -40 ... 80 |
| Temperature °F (short term) : | -40 ... 175 |
| Temperature °F (continuous) : | -40 ... 140 |

Accessories :

| | |
|----------|---|
| MP 3429 | Mounting plate, for enclosures: (315 x 265 x 1) |
| ARH 2328 | DIN-35 Mounting rail, for enclosures: (260 x 35 x 7) |
| FP 10674 | Wall fastening lug (2 pcs) incl. screws (40 x 88 x 14) |
| DR 316 | DIN-35 Mounting rail, for enclosures: (316 x 35 x 7) |

Ratings :

| | |
|---|-------------------|
| Ingress protection (EN 60529): | IP65; |
| Impact Resistance (EN 62262): | IK07; |
| electrical_insulation : | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815) : | Yes |
| UV resistance : | - |
| Flammability Rating : | UL 94 HB |
| Glow Wire Test (IEC 695-2-1) °C : | 650C |

Certificates :

Certificate FI 40343