

## T-slot milling cutter HSSE Co 5

**ORION**<sup>®</sup>

### Application:

for cutting T-slots conforming to DIN 650

### Execution:

- straight shank in accordance with DIN 1835 B
- type NF
- rough machining-finishing teeth
- right-hand twist, approx. 25°
- in accordance with DIN 650



<b>Art. no.</b>	<b>15794 160</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	15794160
<b>Cutting material</b>	HSSE Co5
<b>Surface</b>	Uncoated
<b>Type</b>	NF
<b>Number of cutting edges</b>	8 PCS
<b>Tool holding device</b>	HB parallel shank
<b>Cutting edge diameter</b>	28 mm
<b>Width of cutting edge</b>	12 mm
<b>Suitable for T-groove</b>	16 mm
<b>Length</b>	85 mm
<b>Neck diameter</b>	13 mm
<b>Shank diameter</b>	16 mm
<b>fz steel 700</b>	0.06 mm
<b>Gross Weight</b>	0.166 kg
<b>Product Group</b>	106

### EAN

4039247097470