

PDJN clamp holder, negative, right

For copy turning and longitudinal turning using DN indexable insert

ATORN[®]

Application


For copy turning and longitudinal turning using DN indexable insert 55°.

Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type D, 93° pitch angle, 55° tip angle, 0° clearance angle

Advantage

- very slim geometry, optimised for contour turning with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths
- wide range of delivery: suitable for both finishing and roughing



| | |
|---------------------------------------|-------------------|
| Art. No. | 17838 021 |
| ISO name | PDJN R/L 2525 M15 |
| Shaft height | 25 mm |
| Shank width | 25 mm |
| Length | 150 mm |
| Length of head | 34 mm |
| Programming size | 32 mm |
| Suitable for indexable inserts | DN.. 1506.. |
| Tool design | Right |
| DIN | 4983 |

EAN-Code

4050293126822