

## VDE-insulated heavy-duty side cutters with 2-component grip cover

Chrome-plated steel surface, polished



### Application:

For cutting wires and cables.

### Execution:

- Chrome-vanadium heavy-duty steel, forged, oil-hardened
- Precision blades also inductively hardened for all types of wires
- VDE type according to DIN EN 60900

### Advantage:

- Safe, ergonomic and fatigue-free working thanks to two-component handles
- With forged articulated axis for extreme, long-lasting use
- Optimum coordination of cutting angle, transmission ratio and ergonomic handle shape ensure an excellent cutting rate with little force needed
- 20% less force required compared to standard side-cutters



<b>Art. no.</b>	<b>53095 710</b>
<b>Brand</b>	KNIPEX
<b>Manufacturer Part Number</b>	74 06 180
<b>Length</b>	180 mm
<b>Surface</b>	Chrome plated
<b>VDE certified</b>	Yes
<b>Max. medium wire diameter cutting capacity</b>	3.8 mm
<b>Material of handle</b>	2-component plastic
<b>Gross Weight</b>	0.297 kg
<b>Product Group</b>	535

### EAN

4003773022985