



GE  
Lighting



## Single Ended Halogen

T14 FKD 230- 240V

# 88529

---

### Product information

Quartzline® lamps designed for optimum performance in today's precision range of stage, studio and architectural luminaires. Full range up to 24,000 W  
-Range of bases to meet the needs of OEMs -  
Chromised seal protection up to 500° C.

---



## Product data

EAN Code	0043168885294
DUN Code	10043168885291
Bulb Shape	Tubular
Bulb Diameter [mm]	35
Cap/Base	P28s-24
Dimming Capability	Yes
Gross weight per piece [g]	150
Maximum Overall Length [mm]	121
Net weight per piece [g]	131
Brand	General Electric (GE)

## Performance data

Nominal power [W]	1000
Nominal lamp voltage [V]	240
Nominal lumens [lm]	23000
Nominal correlated colour temperature (CCT) [K]	3050
Colour Rendering Index (CRI) [Ra]	100
Rated Life [h]	750
Ballast Required	No
Coil type	C-13
Energy efficiency class (EEC)	C
Light Center Length [mm]	55.5
Weighted energy consumption [kWh/1000h]	1004.06

## Logistic data

Pack Quantity	12
Pallet quantity EUR (PC)	1152
Pallet quantity UK (PC)	1440
Inner pack type	BOX
Outer pack type	OUTER BOX
Outer case size	190 x 350 x 126 (mm)
Layer quantity	144 EUR, 180 UK
Layer quantity EUR	144
Layer quantity UK	180
Product status	Available

## Application areas



Film and Broadcast



Theatre

## Downloads & Links

[Go to the catalog site \(HTTP\)](#)[Entertainment Solution Spectrum Catalogue \(PDF\)](#)[Lighting design tools & calculators \(HTTP\)](#)

## Disclaimer

Special Purpose Lamp, Not suited for household illumination