


Side Cutters and Tip Cutters

Series 800 Maxi



A = length of cutting edges
 B = head width
 C = head thickness
 D = head length



Tip cutter Pointed relieved head	Side cutter Tapered head	Side cutter Oval head
Visibility and accessibility		Robustness, high cutting capacity

Side cutter – oval head



120 mm / 4.724 Inch
 67 g / 2.36 oz.

- This is the most widely used head shape.
- It is robust and size for size offers the highest cutting capacity.

Model	Cut	Dimensions in mm/Inch				Max. cutting capability in mm/Inch Diameter		
		A	B	C	D	Hard wire	Medium hardness	Copper wire
812N	Semi-flush	15	13.5	7.5	21	0.6	1.2	1.8
		.590	.531	.295	.827	.023	.047	.070
896E	Semi-flush	15	13.5	7.5	21	0.6	1.2	1.8
		.590	.531	.295	.827	.023	.047	.070
822N	Flush	15	13.5	7.5	21	–	1.2	1.8
		.590	.531	.295	.827		.047	.070

Wire quality, see P. 38