



## VET M32 SV EPDM

E1458185

VET-GROMMETS, EPDM BLACK, M32, 14-20mm

Single gate seals with strain relief.

Pull the cable through and then pull back for locking.

Fits in sheet metal with wall thickness 1.0-4.0 mm(PG) or 1.3-5.0 mm(Metric)

## Product Properties:

<b>Gastight</b>	No
<b>Degree of protection (IP)</b>	IP67
<b>Watertight</b>	Yes, No
<b>Fire resistant</b>	No
<b>Angle model</b>	No
<b>With strain relief</b>	No
<b>Model</b>	Closed
<b>Material quality</b>	Ethylene-propylene diene monomer rubber (EPDM)
<b>Shrink technique</b>	No
<b>Insert for cable gland</b>	No
<b>Cable entry</b>	Round
<b>Colour</b>	Black
<b>Surface protection</b>	Untreated
<b>Material</b>	Rubber
<b>Halogen free</b>	Yes
<b>Number of cables</b>	1 .
<b>Operating temperature</b>	-40-100 °C

## Dimensions:

<b>Unit</b>	pcs
-------------	-----

<b>OD</b>	39 mm
<b>CD</b>	14-20 mm
<b>BD</b>	32.2 mm
<b>WT</b>	1.3-5 mm
<b>L</b>	21.5 mm
<b>Bore diameter</b>	32.2 mm
<b>For wall thickness</b>	1.3-5 mm
<b>Suitable for cable diameter</b>	14-20 mm
<b>Thread size (metric)</b>	32 .
<b>MOQ</b>	25 .

### **Approvals:**

<b>Degree of protection (IP)</b>	IP67
----------------------------------	------

### **Compliance:**

<b>RoHS</b>	RoHS 3 (2015/863)
<b>Conflict minerals</b>	N/A, Contains no conflict minerals
<b>Reach</b>	No SVHC (Latest)
<b>SCIP</b>	Not Applicable

### **Other information:**

<b>ETIM-Class</b>	EC000879 - Cable entry sleeve
<b>ETIM-Release</b>	7.0
<b>Product Group</b>	VET-grommets
<b>Search Description</b>	VET-HYLSA, EPDM
<b>Alternative SKU</b>	VETM32SVEPDM

### **Logistic information:**

<b>Barcode</b>	733117610203
<b>E-no</b>	E1458185
<b>Country of origin</b>	CN
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales., Non Stock Item, can be on stock but is not a regular stock item.
<b>Stock code</b>	VET M32 SV EPDM
<b>Taric code</b>	40169300
<b>Unit</b>	pcs
<b>MOQ</b>	25 .