

24566-451 EUROPACPRO SIDE PANEL FOR TEXTILE GASKET, TYPE H, HEAVY, HANDLE HOLES, 6 U, 355 MM







KEY FEATURES

For high mechanical demands, 19" bracket, tox-cold welded, Al, 2-mm, clear passivated, front anodized

Versions for EMC textile gasket

PRODUCT ATTRIBUTES

Product Type: Side Panel

Product Family: EuropacPRO

Type: Type H

Rack Height: 6 U

Board Depth: 355 mm

Package Quantity: 2

Depth: 355 mm

ADDITIONAL PRODUCT DETAILS

Side Panel, Type H, with handle holes, tox welded to the 19" bracket for textile gasket.

Side panel and 19" bracket are tox-cold welded together. tox = Clinching technique, without add aids. This takes place with special tools and high pressure.

Please order front handles separately.

9 U version available on request.



North America

All locations +1.763.422.2661 Chat with us: schroff.nyent.com

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us:

schroff.nvent.com

nVent.com

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER