



| | | |
|---------|----|-----|
| REVISED | DR | APP |
| | | |
| | | |



| Length |
|-------------|
| 0.3m+/-10mm |
| 0.5m+/-10mm |
| 1m+/-15mm |
| 1.5m+/-20mm |
| 2m+/-30mm |
| 3m+/-50mm |
| 5m+/-80mm |
| 7m+/-100mm |
| 10m+/-150mm |



Electrical character:
 1. 100% Open/short/Intermittent testing
 2. TEST FLUKE CHANNEL PASS

Note: (Colour Codes)

- White RAL 9003
- Black RAL 9005
- Grey RAL 7044 (standard)

Connection: RJ45 PLUG - RJ 45 PLUG

Cable diameter: 3,5mm

Unshielded

Gold Plated contacts

Data transfer rate: up to 1 Gbps

Cable must pass Fluke test



| | | |
|----|------------|--|
| 1 | CABLE | PATCHCABLE SLIMLINE CAT 6 250 MHz. U/UTP AWG 30/7 (7/0.10BC) x 4P; PVC OD:3.5 +/- 0.15mm |
| 2 | CONNECTORS | SHORT RJ45 8P8C FU* (COLOR: BLUE) |
| 3 | MOLDING | PVC 75A |
| NO | PART NAME | |

| DESCRIPTION | | PATCHCABLE SLIMLINE CAT 6 | | | |
|-------------------------------|----|---------------------------|------------|----------|----------|
| SIZE | A4 | DATE | 13.01.2016 | CHECKED | TOL |
| UNIT | MM | DRAWN | R.Hueller | APPROVED | 08-22300 |
| CUSTOM TARIF NO.: 85444290900 | | | | | |