



Synergy 21 LED light panel 40W RGB+CCT *Milight/Miboxer*



kwh/1000h:	44,00
Lumen:	2800
Watt:	40,0
Nennlebensdauer:	35000 Std.
Schaltzyklen:	25000
Opt. Umgebungstemp.:	25 °C



Product Name: 40W RGB+CCT Panel Light

Model No.: FUTL01

Power: 40W

Working Temperature: -20~60°

Color temperature: 2700~6500K

Luminous Flux: 2800LM

Light Efficiency: 70LM/W

CRI: >80

UGR: <19

Lifespan: 50000h

Beam Angle: 160°

Size: 595*595mm

Energieeffizienzklasse: A



kWh/1000h: 40

Merkmale

Merkmal	Wert
Abstrahlwinkel:	160

Merkmal	Wert
Ampere:	1
CC oder CV:	CV
Dimmbar:	Ja
Grösse:	595*595*12
LED - Gehäusefarbe:	weiß
LED - Gehäusematerial:	Aluminium
Lichtfarbe:	RGB-WW
Lichtfarbe in Kelvin:	2700~6500
Lumen:	2800
UGR:	<19
Volt:	30-40
Gewicht:	3.361 Kg

Weitere Bilder



Brightness adjustable
Color temperature adjustable

Brightness adjustable, Adjust the color color temperature from 2700-6500K, make the light you want

2.4GHz remote control
Smartphone APP control

Wireless remote and smartphone control, realize the multi-functional setting
(*Need WIFI IBox or WIFI Remote for smartphone App control)

Compatible with

FUT089 FUT088 FUT092 B8 B4/T4 B0

High quality LED Chips

Bright and smooth lighting; low power consumption, low luminance decrease and high CRI

>80 CRI | 2800LM Luminous Flux

Fully Sealed design, ultra-thin frame

Fully sealed design; damp proof and anti-mosquito



Aluminum alloy frame

Damp proof and rust-proof, Heat resistant; Durable in use

COMPATIBLE REMOTE SHEET

Product	Compatible Remote

Zubehör

Art.-Nr.	Name
167420	Synergy 21 LED Controller 40 Watt Panel Light Driver RGB+CCT *Milight/Miboxer*