



- Flexible installation by means of alu profile- or mounting bracket system
- High mechanical stability
- Suitable for applications with wide temperature variations

WCS3-CS70-M1

Technical data

General specifications

Length 0.1 ... 314.5 m
 Radius of bend ≥ 300 mm

Ambient conditions

Operating temperature -40 ... 100 °C (-40 ... 212 °F)

Mechanical specifications

Material thickness 0.5 mm
 Tension loading ≤ 5000 N
 Material stainless steel 1.4310
 Thermal expansion coefficient $1.6 \times 10^{-5} / K$
 Mass 240 g / m

Dimensions

