

Product information

30 25 140

- Heavy duty and wear resisting
- Different jaw styles
- Long, half-round jaws
- Chrome vanadium electric steel, forged, oil-hardened

Long Nose Pliers

DIN ISO 5745




General

Article No.	30 25 140
EAN	4003773001980
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	114 g
Dimensions	140 x 56 x 17 mm
Standard	DIN ISO 5745
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw thickness (joint) (T1)	8.0 mm
Tips width (W4)	2.5 mm
Tips thickness (T2)	2.0 mm
Jaw length (L3)	42.0 mm
Head width (W3)	15.0 mm



technical change and errors excepted