

Material
 Spindel
 O-Ring für Spindel
 Handrad
 Betriebsdruck max.
 Temperatur

Messing
 mit Feinregulierung
 NBR
 Kunststoff
 40 bar
 -30 °C bis 110 °C



210.82



213.40

Nadelventile, Außengewinde mit Innenkonus bzw. Innengewinde

Artikel Nr.	Typen Nr.	Gewinde	DN	A mm	B mm	L mm	SW mm
103763	213.40	G 1/4 außen	4	48,0	50,0	45,0	17
103764	213.41	G 3/8 außen	4	48,0	54,0	51,0	22
103765	210.80	G 1/4 innen	4	48,0	48,0	42,0	17
103766	210.81	G 3/8 innen	4	48,0	52,0	51,0	22
103767	210.82	G 1/2 innen	4	48,0	56,0	64,0	27

