


# PXF6051CAG Datasheet

**Product Name // 150 M, OS1 Single Mode, Cabled, Inline fiber connector**

[View Product Page](#)



## // Product Description:

- ⊞ Inline Fiber Connector to LC type connector
- ⊞ Sealed to IP66, IP68, IP69K when mated with compatible connector
- ⊞ no cable options, or pre-terminated from 5M - 450M available
- ⊞ Duplex LC type fiber connector
- ⊞ Choices of OS1, OM1 and OM3 cables for single or multimode
- ⊞ PXP6081 Sealing Cap available separately to maintain IP rating of unmated connectors
- ⊞ Mate with flex fiber connector PXF6050

## // General Information:

Product Configurator:	No
Product Display Title:	Inline Fiber Connector to LC type Connector
Product Family:	Circular Fiber Connectors
Product Series:	6000 Series - Duplex LC Fiber Buccaneer
Pdfbuilder Enabled:	Yes
Diameter Over Coupling Ring Mm:	32mm
Fibre Mode:	OS1
Function:	Inline to Double LC Connector Double Ended Fiber Cable
Ip Rating:	IP66, IP68, IP69K
Max Operating Temperature:	+70°C
Min Operating Temperature:	-25°C
Product Technical Image:	/p/x/pxf6051xxx_diagram.jpg
Package Id:	564

## // Electrical Specifications:

Contact Type:	LC Fiber
---------------	----------

## // Mechanical Specifications:

Coupling Type:	30 Degree coupling
----------------	--------------------

## // Material Information:

Body Material:	Polyamide (PA)
Flamability Rating:	UL94V-0

**// Product PDF Links**

[6000 Series Fiber connectors...](#)

**// Product 3D CAD Model Links**

[PXF6051CAG3D CAD Model](#)