

# Euromas Polyester

## Enclosure, polyester



P 326

Order no.: 04326000

\* = Available on request.

### Characteristics

Colour of enclosure group  
squirrel grey

Protection class  
IP 66

Enclosure Material  
UP-GF 25-30%, PU foamed seal; for details see Technical Information


### Scope of delivery

Lid and base, lid screws made of V2A, earthing screw

### Dimensions

Dimensions  
80 x 75 x 75.5 mm

### Product drawing



### Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

### Technical documentation / Downloads

#### Technical drawings

3D product data in STEP format: Registration necessary  
Product drawing in PDF format: 04326000 P-326.pdf (63.2 KB)  
Product drawing in DXF format: 04326000 P-326.dxf (457.8 KB)  
Drawing for mechanical processing: 04326000 P-326-G.dxf (642.8 KB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable)

20.02.2020

#### Product information

Euromas Polyester GB.pdf (308.6 KB)

glands, ...)

## Works Test Certificates

683 WPZ-Euromas-Polyester DE.pdf (173.4 KB)

683 WPZ-Euromas-Polyester EN.pdf (152.0 KB)

## Matching accessories

---



Capstan-headed screws, sealable

21007935 KP

For P 305-322, P 324-329



Allen cheese-head screw for lid

21007930 IS

For P 305-319, P 324-326, P 329



Wall brackets, screw-on at rear

21004250 WL

For A 114, A 116, A 118, P 305-322, P 324-329



DIN rails DIN EN 60715 TH 15, galvanised steel

21002800\* TS 15

For A 105, P 305, P 326, PK 105



DIN rails DIN EN 60715 G 32, galvanised steel

22001701 TS 32

For M/T 210, M/T 225, P 305, P 326



DIN rails DIN EN 60715 TH 35, galvanised steel

22001702 TS 35

For M/T 210, M/T 225, P 305, P 326



Set of hinges

21007800 SCHD