

### K Type Surface Temperature Thermocouple



Stainless steel sheath with a moulded handle and 1.50metres of coiled extension cable terminated in a miniature thermocouple plug.

- Surface temperature spring loaded thermocouple with copper disc tip
- Copper disc tip
- Maximum Temperature: +850°C
- Probe 4.7mmØ x 80mm long
- Tip 4mmØ

T/C Type	Manufacturer's Part Number	Rapid Part Number
K	XE-3816-001	90-2753