


EBC005



Splitter box

ZDO6H050MSS0000-00STAK120MSS



Application

Special feature	Free from silicone; Gold-plated contacts
Free from silicone	yes

Electrical data

Operating voltage	[V]	< 30 AC/DC; ("supply class 2" to cULus)
Max. current load per module/slot	[A]	4
Max. current load total	[A]	12



Splitter box

ZDO6H050MSS0000-00STAK120MSS

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67; ("enclosure type 1" according to cULus)

Mechanical data

Weight [g]	241.5
Materials	PA
Number of ports splitter box	6
Connector type	M12

Accessories


Accessories (supplied)	Protective caps: 2 labels: 6
------------------------	---------------------------------

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection - Connection

Connector: 1 x M23; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm



Connection



EBC005



Splitter box

ZDO6H050MSS0000-00STAK120MSS

Electrical connection - slot

Connector: 6 x M12; Moulded body: PA; Contacts: gold-plated; Tightening torque: 0.8...1.5 Nm

