



SIMATIC S7-400, CP 440-1 COMMUNICATIONS MODULE FOR POINT TO POINT CONNECTIONS 1 CHANNEL INCL. CONFIG. PACKAGE ON CD

Figure similar

Supply voltage	
Rated value (DC)	
• 5 V DC	Yes
• 24 V DC	Yes
Input current	
from backplane bus 5 V DC, typ.	330 mA
from backplane bus 5 V DC, max.	360 mA
Power losses	
Power loss, typ.	1.7 W
Memory	
Memory requirements per interface in memory card of S7-CPU	1 to 5 Kbytes for parameters
Interfaces	
Number of interfaces	1
Interface physics, RS 422/RS 485 (X.27)	Yes
RS 422/485, cable length, shielded, max.	1 200 m
Point-to-point	
Integrated protocol driver	
— 3964 (R)	Yes
— ASCII	Yes
Transmission speed, RS 422/485	
— with 3964 (R) protocol, max.	115.2 kbit/s
— with ASCII protocol, max.	115.2 kbit/s

Configuration

Configuration software

- STEP 7

Yes; own parameter assignment forms

Dimensions

Width

25 mm

Height

290 mm

Depth

210 mm

Weights

Weight, approx.

600 g

last modified:

12.03.2015