

## Coaxial Cable Connector 11\_N-50-7-5/133\_N

### Description

Straight cable plug

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0504 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU, RoHS	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

### Related Documents

Outline drawing	DOU-00006936
Catalogue drawing	DOU-00006550
Assembly instruction	DOC-0000179331

### Ordering Information

Single package	11_N-50-7-5/133_NE
Bulk 100 pcs package	11_N-50-7-5/133_NH

### Additional Information

Suitable cables	RG_214_/U, RG_393_/U, RG_213_/U
-----------------	---------------------------------