



Designation IEC:

HR 6

Size:..... AA
 Nominal Voltage:..... 1.2 V
 Rated Capacity:..... 2100 mAh
 Internal Resistance DC, fully charged:..... 45 mOhm
 Impedance AC at 1kHz, fully charged:..... 36 mOhm

0.2 C / 1.00 V:..... 2100 mAh
 1.0 C / 0.90 V:..... 1900 mAh
 Max Discharge Current (continuous / 0.8 V):..... 4.2 A

Charge Retention:

After one year 75% of initial capacity at 20° C determined at 0.2 C rate

Dimensions (including shrink sleeve/label):

Diameter a:..... 14.5 ^{-1.0} mm
 Height b:..... 50.5 ^{-1.3} mm
 Shoulder Height c:..... 49.5 ^{-1.3} mm
 Cap Diameter d:..... 5.5 ^{-0.5} mm
 Volume:..... 8 cm³
 Weight approx:..... 29 g
 Energy Density:..... 315 Wh/l
 Specific Energy:..... 90 Wh/kg

Charge Conditions at:

Standard Charge:..... 210 mA, 16 h
 Fast Charge:..... 2100 mA (-dV)
 Trickle Charge (0.03 - 0.05 C):..... 63 – 105 mA

Temperatures (recommended / permissible) at:

Storage:..... -20° C ... 25° C / -20° C ... 40°
 Charge:..... 15° C ... 30° C / 0° C ... 45°
 Fast Charge:..... 15° C ... 30° C / 0° C ... 40°
 Discharge:..... 0° C ... 40° C / 0° C ... 50°

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries