WC26SM Series Crystal




- **Surface Mountable Clock Crystal**
- 32.768 KHz
- **Small Compact Size**
- **RoHS Compliant**



Frequency	32.768 KHz
Tolerance at +25°C	See Part Number Guide for Options
Stability	-0.034 ppm (±0.006)/°²
Aging	±5 ppm/ yr
Shunt Capacitance	1.5 pF
Load Capacitance	12.5 pF Typ (6pF Option)
Motional Capacitance	0.003 pF TYP
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
Equivalent Resistance	50k Ohms Max
Drive Level	1 μW Max
Temperature Coefficient	0.04 ppm / ° C
Insulation Resistance	500 Megaohms Min / DC 100 V
Shock Resistance	±5 ppm Max (Drop test 3 times on a hard board from 75 cm)

Part Number Guide



Please consult with MMD sales department for any other parameters or options.



MMD Monitor/Quartztek


30400 Esperanza, Rancho Santa Margarita, CA, 92688 Phone: (949) 709-5075, Fax: (949) 709-3536, <u>www.mmdcomp.com</u> Sales@mmdcomp.com





Pg 1 of 2

Revision:

Mechanical Details








2.95 [.116] 2.30 [.091] 0.25 [.010]


DIMENSIONS IN BRACKETS ARE IN INCHES

NOTES


- 1. CAN PLATING = Ni
- 2. LEAD PLATING = Sn 95% 98%, Cu 2% 5%

Tape & Reel





PITCH	8.0
TAPE	16.0
REEL	330 [13 IN]
COUNT	1000





NOTES: UNLESS OTHERWISE SPECIFIED

1. Applicable Standards / Specifications
ANSY 1/4.5M, Dimensions and Tolerances
EIA-83-8.8 mm through 200mm Embossed Carrier Taping and 8 mm and 12 mm
Punched Carrier Taping of Surface Mount Components for Automatic Handling.
2. Dimensions are in millimeters.
3. Tolerancos are ±0.1 mm unless otherwise specified.
4. Do not scale drawing.

MMD Monitor/Quartztek

30400 Esperanza, Rancho Santa Margarita, CA, 92688 Phone: (949) 709-5075, Fax: (949) 709-3536, <u>www.mmdcomp.com</u> Sales@mmdcomp.com



WC26SM082812G Revision:

