

shesto™

Ultrasonic Cleaning Tanks - Overview

- Available in 2, 3, 6, 9 & 27 litre tanks
- Removes Dirt, Grease, Corrosion - Used for cleaning Electronic & Mechanical parts
- Degas mode - Removes air after solution change, providing maximum cleaning effectiveness
- Delicate mode - Runs at half power providing a less aggressive cleaning action for fragile items
- Full-power mode - Powerful deep clean that will cleanse heavily contaminated items
- Temperature and Timing mode - Allows the user to set both the fluid temperature and duration of the cleaning cycle
- Tank, lid and housing made from stainless steel
- Comprehensive manual included
- All Shesto Tanks include Stainless Steel basket and both UK & EU plugs



We offer a full repair service both inside and outside of the 1 year return to base warranty period. Our team of Electronic Engineers have many years' experience in Ultrasonic cleaner systems, capable of repairing units to component level.

Shesto Tanks

Available Models

Model Number.	Tank Vol.	Internal Tank Dimensions in (mm) Bath Lip			Heating Power (W)	Frequency (KHz)	Ultrasonic Power (W)
		L	W	H			
UT8021/EUK*	2 Litre	150	137	100	100	40	50
UT8031/EUK*	3 Litre	240	137	100	100	40	100
UT8061/EUK	6 Litre	300	153	150	300	40	150
UT8091/EUK	9 Litre	300	240	150	300	40	200
UT8271/EUK	27 Litre	495	295	195	500	40	500

*Drainage taps only available on 6 litre tanks and above



Digital
Display



Degas
Mode



Timer
Control



Baskets
Included



Delicate
Mode



Drainage
Tap*



Industrial
Use



Temperature
Control



Shesto Ltd.
Sunley House,
Olds Approach,
Watford, UK,
WD18 9TB

+44(0)208 451 6188
sales@shesto.co.uk
www.shesto.com